

# LEDinspect TASK 180 ESSENTIAL





180 Lumen output

Uniformed wide beam of bright white light to help illuminate workspaces



### Flexible mounting options

Use the built-in magnets or integrated hanging hook to enable hands free use



Anti-Slip Coating

Perfect to ensure maximum grip, even in oily conditions



### Bright, durable and hands-free lighting for tight spaces

Illuminate tight spaces and hard-to-reach areas with the OSRAM LEDinspect TASK 180 ESSENTIAL Lamp. This advanced inspection lamp is designed with bright, long-life LEDs that deliver a powerful 180 lumens of light, making it perfect for mechanics, technicians, and DIY enthusiasts who require precision in their workspaces.

It also includes a magnetic base and 360-degree hanging hook for hands-free operation, allowing you to position the lamp easily in any workspace. Encased in durable grippy anti-slip coating, it is built to withstand the rigors of workshop environments. Whether in the garage or on-site, this inspection lamp is your go-to tool for clear, consistent lighting.

## Product family datasheet

### Technical data

	Product inform	ation	General Produc	:t	Electrical Data	ta		
Product description	Application (Ca and Product sp		Global order reference		Nominal watta	age	Nominal voltage	
INSPECTION LAMP	LED inspection	lights	LEDIL426ESN		3 W		4.5 V	
	Photometric D	ata				Physica Dimens	l Attributes & ions	
Product description	Color temperate	ture	Nominal lumin flux	ous	Light color LED	Product	t weight	
INSPECTION LAMP	6500 K		180 lm		White	146.00	g	
							Lifetime Data	
Product description	Length		Width		Height		Guarantee	
INSPECTION LAMP	35.0 mm		62.0 mm		200.0 mm		2 years	
	Capabilities		ation according A	egulatory Information ing Art. 33 of EU Regulation (EC) 1907/2006				
Product description	Technology	Candid substa	late list nce 1	CAS No 1	. of substance	Safe us	e instruction	
INSPECTION LAMP	LED	Lead		7439-9	2-1		ntification of didate List	

Product description	Declaration no. in SCIP database	
INSPECTION LAMP	9aa32106-6894-	
	413e-9d46-	
	45e6b54b08cf	

substance is sufficient to allow safe use of the article.

### Product family datasheet

### Download Data

#### File



User instruction
GPRS\_Safety symbols instructions

### **Application advice**

For more detailed application information and graphics please see product datasheet.

#### **Disclaimer**

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.